

ESSILOR PALs RANGE AVAILABILITY

| | Power Range | Index | Base Curve | Diameter | Add Power |
|---|---------------------|-------|--------------------------------------|--|-------------|
| Accolade Freedom™ | | | | | |
| 1.50 Index Plastic | +6.00 D to -9.00 D | 1.50 | 2.00, 3.00, 4.50, 6.00, 7.00 | Blank size available as finished uncut | .75 to 3.50 |
| 1.50 Transitions® (Gray/Brown) | +6.00 D to -9.00 D | 1.50 | 2.00, 3.00, 4.50, 6.00, 7.00 | | .75 to 3.50 |
| Airwear® | +6.00 D to -10.00 D | 1.59 | 2.00, 3.00, 4.00, 5.50, 6.50 | | .75 to 3.50 |
| Airwear® Transitions® V (Gray/Brown) | +6.00 D to -10.00 D | 1.59 | 2.00, 3.00, 4.00, 5.50, 6.50 | | .75 to 3.50 |
| Thin&Lite® 1.67 | +8.00 D to -12.00 D | 1.67 | 2.00, 3.00, 4.00, 5.50, 6.50 8.00 | | .75 to 3.50 |
| Thin&Lite® 1.67 Transitions® V (Gray/Brown) | +8.00 D to -12.00 D | 1.67 | 2.00, 3.00, 4.00, 5.50, 6.50 8.00 | | .75 to 3.50 |
| Accolade™ | | | | | |
| 1.50 Index Plastic | +6.00 D to -9.00 D | 1.50 | 2.00, 3.00, 4.50, 6.00, 7.00 | 80/85 mm | .75 to 3.50 |
| 1.50 Transitions (Gray/Brown) | +6.00 D to -9.00 D | 1.50 | 2.00, 3.00, 4.50, 6.00, 7.00 | 77/82 mm | .75 to 3.50 |
| Airwear | +6.00 D to -10.00 D | 1.59 | 2.00, 3.00, 4.00, 5.50, 6.50 | 80/85 mm | .75 to 3.50 |
| Airwear Transitions V (Gray/Brown) | +6.00 D to -10.00 D | 1.59 | 2.00, 3.00, 4.00, 5.50, 6.50 | 77/82 mm | .75 to 3.50 |
| Thin&Lite 1.67 | +8.00 D to -12.00 D | 1.67 | 2.00, 3.00, 4.00, 5.50, 6.50 8.00 | 75/80 mm 70/75 mm | .75 to 3.50 |
| Thin&Lite 1.67 Transitions V (Gray/Brown) | +8.00 D to -12.00 D | 1.67 | 2.00, 3.00, 4.00, 5.50, 6.50 8.00 | 75/80 mm 70/75 mm | .75 to 3.50 |
| Ovation® | | | | | |
| 1.50 Index Plastic | +6.00 D to -10.00 D | 1.50 | 1.75, 3.00, 4.50, 6.00, 7.00 | 80/85 mm | .75 to 3.50 |
| 1.50 Transitions (Gray/Brown) | +6.00 D to -10.00 D | 1.50 | 1.75, 3.00, 4.50, 6.00, 7.00 | 77/82 mm | .75 to 3.50 |
| Airwear | +6.00 D to -10.00 D | 1.59 | 1.75, 3.00, 4.50, 5.50, 6.50 | 80/85 mm | .75 to 3.50 |
| Airwear Transitions V (Gray/Brown) | +6.00 D to -10.00 D | 1.59 | 1.75, 3.00, 4.50, 5.50, 6.50 | 78/83 mm | .75 to 3.50 |
| Airwear Polarized (Gray/Brown) | +6.00 D to -10.00 D | 1.59 | 1.75, 3.00, 4.50, 5.50, 6.50 | 75/80 mm | .75 to 3.50 |
| Thin&Lite 1.67 HC | +8.00 D to -12.00 D | 1.67 | 1.75, 3.00, 4.50, 5.50, 6.50 8.00 | 75/80 mm 70/75 mm | .75 to 3.50 |
| Thin&Lite 1.67 Transitions V (Gray) | +8.00 D to -12.00 D | 1.67 | 1.75, 3.00, 4.50, 5.50, 6.50 8.00 | 75/80 mm 70/75 mm | .75 to 3.50 |

Accolade Freedom

- Faster adaptation
- Freedom in your choice of frames
- Reduced distortion versus traditional surfacing
- Enhances visual fields, providing more natural vision

Accolade

- Faster adaptation
- Allows wider acuity fields for myopes
- Provides softer periphery for hyperopes
- Balances natural vision for low ametropes

Ovation

- Customized design to specific Rx
- Eliminates annoying distortions
- Accommodates wearer's prescription for comfortable reading

ESSILOR PALs RANGE AVAILABILITY

| | Power Range | Index | Base Curve | Diameter | Add Power |
|--------------------------------------|---------------------|-------|-------------------------------------|----------------------|--------------|
| SmallFit™ | | | | | |
| Airwear® | +6.00 D to -10.00 D | 1.59 | 1.75, 3.00, 4.50, 5.50, 6.50 | 75/80 mm | .75 to 3.00 |
| Airwear® Transitions® V (Gray/Brown) | +6.00 D to -10.00 D | 1.59 | 1.75, 3.00, 4.50, 5.50, 6.50 | 74/79 mm | .75 to 3.00 |
| Essilor Natural® | | | | | |
| 1.50 Index Plastic | +6.00 D to -10.00 D | 1.50 | 1.75, 3.75, 5.50, 6.50, 7.50 | 80/85 mm | .75 to 3.50 |
| 1.50 Transitions® (Gray) | +6.00 D to -10.00 D | 1.50 | 1.75, 3.75, 5.50, 6.50, 7.50 | 77/82 mm | .75 to 3.50 |
| Airwear | +6.00 D to -10.00 D | 1.59 | 1.75, 3.75, 5.50, 7.25 | 80/85 mm | .75 to 3.00 |
| Airwear Transitions V (Gray) | +6.00 D to -10.00 D | 1.59 | 1.75, 3.75, 5.50, 7.25 | 78/83 mm | .75 to 3.00 |
| Thin&Lite® 1.60 | +8.00 D to -10.00 D | 1.60 | 1.75, 3.75, 5.50, 7.25 8.50 | 80/85 mm 70/75 mm | .75 to 3.50 |
| 1.60 High Index Glass | +6.00 D to -7.50 D | 1.60 | 3.50, 5.25, 6.75 | 70/75 mm | .75 to 3.50 |
| 1.60 High Index PhotoGray Extra® | +6.00 D to -7.50 D | 1.60 | 3.50, 5.25, 6.75 | 70/75 mm | .75 to 3.50 |
| Adaptar® | | | | | |
| 1.50 Index Plastic | +7.00 D to -10.00 D | 1.50 | 2.25, 4.25, 6.25, 8.25 5.00 | 80 mm 80/85 mm | .75 to 3.50 |
| 1.50 Transitions (Gray) | +7.00 D to -10.00 D | 1.50 | 2.25, 4.25, 6.25, 8.25 5.00 | 77 mm 77/82 mm | .75 to 3.50 |
| Airwear | +6.50 D to -10.00 D | 1.59 | 2.25, 4.25, 5.50, 7.25 | 80/85 mm | 1.00 to 3.00 |
| Thin&Lite 1.60 | +8.00 D to -12.00 D | 1.60 | 2.25, 4.25, 5.00, 7.25 .50, 8.25 | 80/85 mm 80 mm | .75 to 3.50 |
| Clear Glass | +6.00 D to -10.00 D | 1.53 | 2.00, 4.00, 6.00, 8.00 | 70/75 mm | .75 to 3.50 |
| PhotoGray Extra Glass | +6.00 D to -10.00 D | 1.53 | 2.00, 4.00, 6.00, 8.00 | 70/75 mm | .75 to 3.50 |

SmallFit

- Provides wearers a greater choice of small frame designs
- Customized to wearer's prescription and addition
- Soft design provides comfortable intermediate vision

Essilor Natural

- Balances increased add power, delivering greater comfort and clarity
- Offers a wide near zone, minimizing unnatural head movement
- Aids in reducing the "swim" effect

Adaptar

- Optimum peripheral clarity and wearer comfort
- Easy adaptation for every stage of presbyopia
- Offers good value when price is a concern

